

## Image gallery

## 3D view



## Part No: 15-005623

## Product Description

- IP67 Combination D-SUB
- 5W1 [•••••]
- Female Connector

[Inquiry](#)

## General Data

## Technical Data

## Material Data

## Standards

## Downloads

|                                         |                 |
|-----------------------------------------|-----------------|
| Dielectric with standing voltage signal | 1000 V          |
| Dielectric with standing voltage power  | 1000 V          |
| min. working temperature                | -25° C          |
| max. working temperature                | +105° C         |
| Working voltage power                   | 250 V           |
| Quality class                           | Quality class 3 |
| Mating cycles                           | 50              |
| Current rating power                    | 20 A            |
| Insertion force                         | 66 N            |
| Extraction force                        | 44 N            |
| Power resistance standard               | 2,7 mOhm        |