

## Image gallery

## 3D view



## Part No: 15-007103

## Product Description

- IP67 Combination D-SUB
- 7W2 [o\*\*\*\*\*o]
- Socket

[Inquiry](#)

## General Data

## Technical Data

## Material Data

## Standards

## Downloads

|                                         |                             |
|-----------------------------------------|-----------------------------|
| Dielectric with standing voltage signal | 1000 V                      |
| Dielectric with standing voltage power  | 1000 V                      |
| min. working temperature                | -40° C                      |
| max. working temperature                | +105° C                     |
| Working voltage power                   | 250 V                       |
| Quality class                           | Quality class 3             |
| Mating cycles                           | 50                          |
| IP rating                               | IP67 in connected condition |
| Current rating power                    | 20 A                        |
| Power resistance standard               | 1 mOhm                      |