




pin assignment:

- 1) white
- 2) brown
- 3) green
- 4) yellow
- 5) red
- 6) blue
- 7) grey
- 8) pink
- 9) -

part-no.:	length L:	cable:
15-008153	2m	LIYCY (TP) 4x2x0,25mm² UL2464 cable: 781-GAQ280T
15-008163	4m	
15-008173	5m	

NOTES:

1. IP RATING: IP 20
2. METAL SHELL: ZINC DIE CAST;
min. 50µin NICKEL PLATING over COPPER
3. INSULATORS: PBT GF UL 94 V-0; BLACK
4. SEALING COMPOUND: EPOXY RESIN UL 94 V-0; BLACK
5. CONTACTS: COPPER ALLOY; GOLD FLASH over NICKEL
6. COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
7. HEXLOCKING SCREWS: STAINLESS STEEL
8. OVERMOLDING: TECHNOMELT; BLACK
9. RECOMMENDED TORQUE FOR MOUNTING SCREW
35Ncm (3.1 in.LB) / max.67Ncm (6 in.LB)
10. CONNECTOR IS PART MARKED: [PART NO. CONEC ABC]

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND				tolerance		 dim. in mm	scale: 2:1 (4:1)					
							material: SEE NOTES					
								date	name	title: D-SUB MALE 9pos. MOLDED with open 4-40 UNC threaded		
								drawn 25.01.2016	Heinrich			
								appd. 26.02.2016	Fischer			
								norm				
								d-old				
										dwg no:		DIN-A3
				a	Original					15K1A1704		sh: 1
				rev.	description	date	name			part no:		SEE TABLE



RoHS compliant