



Part No: 16-002111

Product Description

- D-SUB Standard
- 25-pos.
- Plug
- Solder pin straight
- Threaded rear spacer
- Quality class 1

[Inquiry](#)

[Show related parts](#)

General Data	Technical Data	Material Data	Standards	Downloads
--------------	----------------	---------------	-----------	-----------

Dielectric with standing voltage signal	1000 V
Quality class	Quality class 1
Mating cycles	500
IP rating	IP 20
Insertion force	<83 N
Contact resistance standard	10 mOhm
min. working temperature	-55° C
max. working temperature	+125° C

Suitable Products

