



Part No: 16-002161

Product Description

- D-SUB Standard
- 25-pos.
- Socket
- Solder pin straight
- Threaded rear spacer
- Quality class 1

[Inquiry](#)

[Show related parts](#)

General Data	Technical Data	Material Data	Standards	Downloads
Dielectric with standing voltage signal		1000 V		
Quality class		Quality class 1		
Mating cycles		500		
IP rating		IP 20		
Insertion force		<83 N		
Contact resistance standard		10 mOhm		
min. working temperature		-55° C		
max. working temperature		+125° C		

Suitable Products

