Image gallery | 3D view



Part No: 164A10379X

Product Description

- D-SUB Standard
- 15-pos.
- Socket
- Solder pin straight
- Threaded Insert
- Quality class 3
- M3

Inquiry

General Data | Technical Data | Material Data | Standards | Downloads

Dielectric with standing voltage signal	1000 V
Quality class	Quality class 3
Mating cycles	50
IP rating	IP 20
Insertion force	<50 N
Extraction force	<50 N
Contact resistance standard	10 mOhm
min. working temperature	-55° C
max. working temperature	+125° C