







2 CONTACTS WILL BE SUPPLIED LOOSE

STRIPPING DIMENSIONS



NOTES:

1. MATERIAL AND FINISH:

- COUPLER RING: PA GF (BLACK); UL94 V-0; UL (f1) RATED
- PLUG HOUSING: PA GF (BLACK); UL94 V-0; UL (f1) RATED
- CABLE GLAND: PA (BLACK), UL94 V-0; UL (f1) RATED
- CABLE GLAND RUBBER RING: NBR; COLOR: BLACK
- CABLE FITTING: PA (BLACK); UL94 V-0; UL (f1) RATED
- INTERFACIAL SEAL: SILICONE; COLOR: WHITE
- RETAINING RING: STAINLESS STEEL

2. HIGH POWER CONTACTS; CRIMP; 30A

- FOR USE WITH CABLE AWG 8* - 10
- MATERIAL: COPPER ALLOY
- PLATING, MATING AREA: GOLD FLASH over NICKEL
- PLATING, TERMINATION SIDE: 160-240µin TIN over 80µin NICKEL
- CONTACTS WILL BE SUPPLIED LOOSE
- CRIMPING: USE CRIMP TOOL 360X10409X WITH TOOL INSERT 360X20029X

SELECTOR SETTINGS: 5 FOR AWG 8*; 4 FOR AWG 10

3. OPERATING TEMPERATURE: -40°C to +100°C

4. WORKING VOLTAGE: 48V AC/DC

5. IP67 RATED WHEN COVERED OR FULLY MATED WITH THE APPROPRIATE MATING CONNECTOR

6. *NOTE: FOR AWG 8 STRANDED 19/21, 37/24 and 65/26 WIRE ONLY

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND				dim. in mm		scale: 1,5:1
				material: SEE NOTES		
				title: IP67 POWER BAYONET 2pos. PLUG KIT / CRIMP cable mount Ø13-18mm		
				dwg no: 17K1A473		DIN-A3
rev. description date name				part no: 17-400563		sh: 1
a Original				CONEC®		
norm				date 27.10.15 name Lehmenkühler		
appd. 27.10.15 Koch				d-old		

RoHS compliant