


FLATCABLE CONNECTORS


Dip connector – 4 to 40 positions




RoHS compliant

- DESCRIPTION**
- Insulation displacement termination (IDC)
 - Contact spacing 2.54 mm
 - Contact plating: gold or tin plated

PRODUCT DRAWING



PCB-hole pattern



No. of Pos.	A ± 0.1	B ± 0.2	C ± 0.1	D ± 0.1
4	2.54	8.41	7.62	10.7
6	2x2.54=5.08	10.95	7.62	10.7
8	3x2.54=7.62	13.49	7.62	10.7
10	4x2.54=10.16	16.03	7.62	10.7
12	5x2.54=12.70	18.57	7.62	10.7
14	6x2.54=15.24	21.11	7.62	10.7
16	7x2.54=17.78	23.56	7.62	10.7
18	8x2.54=20.32	26.19	7.62	10.7
20	9x2.54=22.86	28.73	7.62	10.7
22	10x2.54=25.40	31.35	10.16	13.2
24	11x2.54=27.94	33.60	15.24	18.3
28	13x2.54=33.02	38.97	15.24	18.3
32	15x2.54=38.10	44.05	15.24	18.3
36	17x2.54=43.18	49.13	15.24	18.3
40	19x2.54=48.26	53.90	15.24	18.3

ORDER DATA

(Dim. = mm)

No. of Pos.	gold plated	tin plated	No. of Pos.	gold plated	tin plated
4	220 A 10019 X	220 F 10019 X	20	220 A 10099 X	220 F 10099 X
6	220 A 10029 X	220 F 10029 X	22	220 A 10109 X	220 F 10109 X
8	220 A 10039 X	220 F 10039 X	24	220 A 10119 X	220 F 10119 X
10	220 A 10049 X	220 F 10049 X	28	220 A 10129 X	220 F 10129 X
12	220 A 10059 X	220 F 10059 X	32	220 A 10139 X	220 F 10139 X
14	220 A 10069 X	220 F 10069 X	36	220 A 10149 X	220 F 10149 X
16	220 A 10079 X	220 F 10079 X	40	220 A 10159 X	220 F 10159 X
18	220 A 10089 X	220 F 10089 X			