


Solder pin – Angled – Precision machined contacts – .625" / 15.88 mm connector spacing



- Variations: plug – plug; socket – socket; plug – socket
- Mounting styles:
 - with mounting bracket and 4-40 UNC threaded insert
 - with mounting bracket and 4-40 UNC front spacer
- Quality class 3 (also available in quality class 1)
- Shell: Steel tin plated (brass tin plated on request)



PCB layout: Kat1iU5A / Kat1iU6A

Technical drawing of a 4-60 UNC nut, showing a side view with dimensions: 3.2, 7.19±0.2, 15.76±0.2, 18.8 max, and 4-60 UNC.


Technical drawing of a 4-40 UNC nut. The drawing shows a side view of the nut with dimensions: 3.2 (width of the top flange), 7.10 ± 0.2 (height of the top flange), 15.76 ± 0.7 (height of the main body), and 7.3 (height of the bottom flange). The thread is labeled 4-40 UNC. The bottom flange has two mounting holes with a diameter of 0.4.

C-FILTER D-SUB STANDARD – DUAL PORT

Solder pin – Angled – Precision machined contacts – .625" / 15.88 mm connector spacing

ORDER DATA

Capacitance 370 pF

VERSION WITH 4-40 UNC THREADED INSERT				VERSION WITH 4-40 UNC FRONT SPACER			
No. of pos.	Design	Part Number		No. of pos.	Design	Part Number	
	09/09	Plug upper / Plug bottom	241 A 14130 X	09/09	Plug upper / Plug bottom	241 A 14370 X	
	15/15	Plug upper / Plug bottom	241 A 14140 X	15/15	Plug upper / Plug bottom	241 A 14380 X	
	25/25	Plug upper / Plug bottom	241 A 14150 X	25/25	Plug upper / Plug bottom	241 A 14390 X	
	37/37	Plug upper / Plug bottom	241 A 14160 X	37/37	Plug upper / Plug bottom	241 A 14400 X	
	09/09	Plug upper / Socket bottom	241 A 14250 X	09/09	Plug upper / Socket bottom	241 A 14490 X	
	15/15	Plug upper / Socket bottom	241 A 14260 X	15/15	Plug upper / Socket bottom	241 A 14500 X	
	25/25	Plug upper / Socket bottom	241 A 14270 X	25/25	Plug upper / Socket bottom	241 A 14510 X	
	37/37	Plug upper / Socket bottom	241 A 14280 X	37/37	Plug upper / Socket bottom	241 A 14520 X	
	09/09	Socket upper / Socket bottom	242 A 14020 X	09/09	Socket upper / Socket bottom	242 A 14260 X	
	15/15	Socket upper / Socket bottom	242 A 14030 X	15/15	Socket upper / Socket bottom	242 A 14270 X	
	25/25	Socket upper / Socket bottom	242 A 14040 X	25/25	Socket upper / Socket bottom	242 A 14280 X	
	37/37	Socket upper / Socket bottom	242 A 14050 X	37/37	Socket upper / Socket bottom	242 A 14290 X	
	09/09	Socket upper / Plug bottom	242 A 14140 X	09/09	Socket upper / Plug bottom	242 A 14380 X	
	15/15	Socket upper / Plug bottom	242 A 14150 X	15/15	Socket upper / Plug bottom	242 A 14390 X	
	25/25	Socket upper / Plug bottom	242 A 14160 X	25/25	Socket upper / Plug bottom	242 A 14400 X	
	37/37	Socket upper / Plug bottom	242 A 14170 X	37/37	Socket upper / Plug bottom	242 A 14410 X	

Capacitance 830 pF

VERSION WITH 4-40 UNC THREADED INSERT				VERSION WITH 4-40 UNC FRONT SPACER			
No. of pos.	Design	Part Number		No. of pos.	Design	Part Number	
	09/09	Plug upper / Plug bottom	241 A 14210 X	09/09	Plug upper / Plug bottom	241 A 14450 X	
	15/15	Plug upper / Plug bottom	241 A 14220 X	15/15	Plug upper / Plug bottom	241 A 14460 X	
	25/25	Plug upper / Plug bottom	241 A 14230 X	25/25	Plug upper / Plug bottom	241 A 14470 X	
	37/37	Plug upper / Plug bottom	241 A 14240 X	37/37	Plug upper / Plug bottom	241 A 14480 X	
	09/09	Plug upper / Socket bottom	241 A 14330 X	09/09	Plug upper / Socket bottom	241 A 14570 X	
	15/15	Plug upper / Socket bottom	241 A 14340 X	15/15	Plug upper / Socket bottom	241 A 14580 X	
	25/25	Plug upper / Socket bottom	241 A 14350 X	25/25	Plug upper / Socket bottom	241 A 14590 X	
	37/37	Plug upper / Socket bottom	241 A 14360 X	37/37	Plug upper / Socket bottom	241 A 14600 X	
	09/09	Socket upper / Socket bottom	242 A 14100 X	09/09	Socket upper / Socket bottom	242 A 14340 X	
	15/15	Socket upper / Socket bottom	242 A 14110 X	15/15	Socket upper / Socket bottom	242 A 14350 X	
	25/25	Socket upper / Socket bottom	242 A 14120 X	25/25	Socket upper / Socket bottom	242 A 14360 X	
	37/37	Socket upper / Socket bottom	242 A 14130 X	37/37	Socket upper / Socket bottom	242 A 14370 X	
	09/09	Socket upper / Plug bottom	242 A 14220 X	09/09	Socket upper / Plug bottom	242 A 14460 X	
	15/15	Socket upper / Plug bottom	242 A 14230 X	15/15	Socket upper / Plug bottom	242 A 14470 X	
	25/25	Socket upper / Plug bottom	242 A 14240 X	25/25	Socket upper / Plug bottom	242 A 14480 X	
	37/37	Socket upper / Plug bottom	242 A 14250 X	37/37	Socket upper / Plug bottom	242 A 14490 X	

Capacitance 1300 pF

VERSION WITH 4-40 UNC THREADED INSERT				VERSION WITH 4-40 UNC FRONT SPACER			
No. of pos.	Design	Part Number		No. of pos.	Design	Part Number	
	09/09	Plug upper / Plug bottom	241 A 14170 X	09/09	Plug upper / Plug bottom	241 A 14410 X	
	15/15	Plug upper / Plug bottom	241 A 14180 X	15/15	Plug upper / Plug bottom	241 A 14420 X	
	25/25	Plug upper / Plug bottom	241 A 14190 X	25/25	Plug upper / Plug bottom	241 A 14430 X	
	37/37	Plug upper / Plug bottom	241 A 14200 X	37/37	Plug upper / Plug bottom	241 A 14440 X	
	09/09	Plug upper / Socket bottom	241 A 14290 X	09/09	Plug upper / Socket bottom	241 A 14530 X	
	15/15	Plug upper / Socket bottom	241 A 14300 X	15/15	Plug upper / Socket bottom	241 A 14540 X	
	25/25	Plug upper / Socket bottom	241 A 14310 X	25/25	Plug upper / Socket bottom	241 A 14550 X	
	37/37	Plug upper / Socket bottom	241 A 14320 X	37/37	Plug upper / Socket bottom	241 A 14560 X	
	09/09	Socket upper / Socket bottom	242 A 14060 X	09/09	Socket upper / Socket bottom	242 A 14300 X	
	15/15	Socket upper / Socket bottom	242 A 14070 X	15/15	Socket upper / Socket bottom	242 A 14310 X	
	25/25	Socket upper / Socket bottom	242 A 14080 X	25/25	Socket upper / Socket bottom	242 A 14320 X	
	37/37	Socket upper / Socket bottom	242 A 14090 X	37/37	Socket upper / Socket bottom	242 A 14330 X	
	09/09	Socket upper / Plug bottom	242 A 14180 X	09/09	Socket upper / Plug bottom	242 A 14420 X	
	15/15	Socket upper / Plug bottom	242 A 14190 X	15/15	Socket upper / Plug bottom	242 A 14430 X	
	25/25	Socket upper / Plug bottom	242 A 14200 X	25/25	Socket upper / Plug bottom	242 A 14440 X	
	37/37	Socket upper / Plug bottom	242 A 14210 X	37/37	Socket upper / Plug bottom	242 A 14450 X	