



Part No: 2F2CSA22S58K40X

Product Description

- Filter Combination D-SUB
- 2W2C [o/o]
- Socket
- C-Filter
- 47 nF
- Threaded Insert

Inquiry

General Data	Technical Data	Material Data	Standards	Downloads
Dielectric with standing voltage power		707 V DC		
Capacitor value power contact		47 nF		
Working voltage power		100 V DC		
Quality class		Quality class 3		
Mating cycles		50		
IP rating		IP 20		
Current rating power		40 A		
Insertion force		14 N		
Extraction force		14 N		
min. working temperature		-55° C		
max. working temperature		+125° C		
Filter type		C		