

Image gallery

3D view



Part No: 2F2CSA28S42A10X

Product Description

- Filter Combination D-SUB
- 2W2C [o/o]
- Socket
- C-Filter
- 100 nF
- Through hole

[Inquiry](#)

General Data

Technical Data

Material Data

Standards

Downloads

Dielectric with standing voltage power	707 V DC
Capacitor value power contact	100 nF
Power contact cross section	AWG 12- 14
Working voltage power	100 V DC
Quality class	Quality class 3
Mating cycles	50
IP rating	IP 20
Current rating power	20 A
Insertion force	14 N
Extraction force	14 N
min. working temperature	-55° C
max. working temperature	+125° C
Filter type	C