












used for: D-SUB



POS.	A	B	C	D	E	Colour	Part-No.
9	30.5	16	41	25	7	grey	300X10169X
						metallized	300X10109X
15	40	16.2	37.4	33.3	9.9	grey	300X10179X
						metallized	300X10119X
25	55	16.5	44.5	47	10.7	grey	300X10209X
						metallized	300X10149X










THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
1 x e	Ä 6582	15.03.2017	Lehmen
2 x d	Ä 6248	05.08.2016	Unkr.
1 x c	Ä 2309	07.09.2005	Lehmen
2 x b	Ä 2298	19.08.2005	Lehmen

tolerance		
.X	±0.30	
.XX	±0.20	
.XXX	±0.10	
1995	date	name
drawn	30.60.	Barcinski
appd.	30.06.	Mickenbecker
1. norm		
d-old		
		

scale:	2:1
material:	
title:	TWO-PIECE SHELL HOOD 9-25pos. with short screw
dwg no:	16V1103A
part no:	SEE TABLE
DIN-A	3
sh:1/4	

RoHS compliant



used for:


D-SUB









Colour	Part-No.
grey	300X10219X
metallized	300X10159X

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND				tolerance			scale: 2:1		
				X	±0.30		dim. in mm	material:	
				.XX	±0.20			title: TWO-PIECE SHELL HOOD 37pos. with short screw	
				.XXX	±0.10				dwg no:
				1995	date	name	16V1103A	3	
				drawn	30.60.	Barcinski			sh:2/4
				appd.	30.06.	Mickenbecker			
				norm					
2 x d	Ä 6248	05.08.2016	Unkr.	d-old					
1 x c	Ä 2309	07.09.2005	Lehmen.						
2 x b	Ä 2298	19.08.2005	Lehmen.						
rev.	description	date	name						

RoHS compliant

CONEC





(d)

Colour	Part-No.
grey	300X10869X
metallized	300X10919X

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
2 x d	Ä 6248	05.08.2016	Unkr.
1 x c	Ä 2309	07.09.2005	Lehmen
2 x b	Ä 2298	19.08.2005	Lehmen

tolerance		
x	±0.30	
xx	±0.20	
xxx	±0.10	
dim. in mm		
1995	date	name
drawn	30.06.	Barcinski
appd.	30.06.	Mickenbecker
norm		
d-old		



scale:	2:1
material:	
title:	TWO-PIECE SHELL HOOD 37pos. with long screw
dwg no:	16V1103A
part no:	SEE TABLE
DIN-A	3
sh:4/4	