Image gallery | 3D view

Part No: 3013W6SAM99A20X

Product Description

- D-SUB Combination Standard
- 13W6 [•••••••○○○○○○]
- Socket
- Solder cup
- Threaded Insert
- M3

Inquiry

General Data | Technical Data | Material Data | Standards | Downloads

Dielectric with standing voltage signal	1000 V
min. working temperature	-55° C
Quality class	Quality class 3
Mating cycles	50
IP rating	IP 20
Extraction force	43 N
Contact resistance standard	8 mOhm