







Part No: 3017W2PXK99A30X

Product Description

- D-SUB Combination Standard
- 17W2 [○••••••••••••••• ○]
- Plug
- Crimp
- Threaded Insert
- UNC 4-40

Inquiry

General Data	Technical Data	Material Data	Standards	Downloads

Dielectric with standing voltage signal	1000 V
min. working temperature	-55° C
IP rating	IP 20
Extraction force	17 N
Contact resistance standard	8 mOhm