



Part No: 3017W2SAM99A30X

Product Description

- D-SUB Combination Standard
- 17W2 [ø.....ø]
- Socket
- Solder cup
- Threaded Insert
- UNC 4-40

[Inquiry](#)

General Data	Technical Data	Material Data	Standards	Downloads
Dielectric with standing voltage signal	1000 V			
min. working temperature	-55° C			
Quality class	Quality class 3			
Mating cycles	50			
IP rating	IP 20			
Extraction force	17 N			
Contact resistance standard	8 mOhm			