



Part No: 302A10879X

Product Description

- D-SUB High Density
- 26-pos.
- Socket
- Solder Pin angled .350" stamped Contacts
- Plastic bracket
- Quality class 3
- UNC 4-40

[Inquiry](#)

General Data

Technical Data

Material Data

Standards

Downloads

Dielectric with standing voltage signal	1000 V
Quality class	Quality class 3
Mating cycles	50
IP rating	IP 20
Insertion force	<84 N
min. working temperature	-55° C
max. working temperature	+125° C