

Image gallery

3D view



Part No: 302A11249X

Product Description

- D-SUB Standard
- 9-pos.
- Socket
- Solder Pin angled .318" stamped Contacts
- Plastic bracket
- Quality class 3
- UNC 4-40

Inquiry

General Data

Technical Data

Material Data

Standards

Downloads

Dielectric with standing voltage signal	1000 V
Quality class	Quality class 3
Mating cycles	50
IP rating	IP 20
Insertion force	<30 N
Extraction force	<30 N
min. working temperature	-55° C
max. working temperature	+125° C