

Image gallery

3D view



Part No: 320X12559X

Product Description

- D-SUB Standard
- 37-pos.
- Adapter - Gender Changer
- Quality class 3
- UNC 4-40

Inquiry

General Data

Technical Data

Material Data

Standards

Downloads

Dielectric with standing voltage signal	1000 V
Quality class	Quality class 3
Mating cycles	50
IP rating	IP 20
Insertion force	<123 N
Extraction force	<123 N
Contact resistance standard	10 mOhm
min. working temperature	-25° C
max. working temperature	+85° C