



Part No: 3H45W2SAM62A30X

Product Description

- D-SUB Combination High Density
- 45W2 [.....]
- Socket
- Solder cup
- Threaded Insert
- UNC 4-40
- 50 Ohm
- Crimp / crimp angled

[Inquiry](#)

General Data	Technical Data	Material Data	Downloads
Dielectric with standing voltage signal		1000 V	
Dielectric with standing voltage power		1000 V	
Dielectric with standing voltage coaxial		750 V	
Working voltage power		250 V	
Working voltage coaxial		250 V	
IP rating		IP 20	
Current rating power		20 A	
Impedance coax		50 Ohm	
Frequency range		0- 2 Ghz	
min. working temperature		-55° C	
max. working temperature		+125° C	
Quality class		Quality class 3	
Mating cycles		50	