



Part No: 41-40023

SAL-7/8-FK4PE-P10

Product Description

- Sockets
- Female connector axial
- 7/8
- 4-pos.+PE
- 10 mm
- Front panel mounting
- Solder pin straight
- Unshielded

[Inquiry](#)

General Data

Technical Data

Material Data

Standards

Downloads

Shielding	Unshielded
min. working temperature	-30° C [UL: -30° C]
max. working temperature	+80° C [UL: +75° C]
Pollution degree	3/2
IP rating	IP67
Sealing material	FPM
Mating cycles	>=100
Insulation resistance	>=100M Ohm