



Part No: 42-10163

SAL-8-RK4-RS4-1,5/K1

Product Description

- M8x1
- A-coded
- Overmoulded Connectors
- Female connector axial
- Double ended
- 4- pos.
- Unshielded
- 1,5 m
- 0,25 mm²
- TPU halogeenfree high flexible

Inquiry

General Data	Technical Data	Material Data	Standards	Downloads
Shielding	Unshielded			
Cable quality	Li9Y11Y			
Wire cross section	0,25 mm²			
min. working temperature	-30° C [UL: -30° C]			
max. working temperature	+80° C [UL: +50° C]			
Pollution degree	3/2			
IP rating	IP67			
Sealing material	FPM			
Cable quality [e.g. PP, PVC, TPE etc.]	TPU halogeenfree high flexible			
Mating cycles	>=100			
Recommended torque	0,4 Nm			
Insulation resistance	>=100M Ohm			
Cable color	Black			