

Image gallery

3D view



Part No: 43-00415

SAL-12B-RSC4-C/050

Product Description

- Male connector axial
- Crimp
- M12x1
- Profibus DP
- Shielded
- Copper Alloy
- B-coded
- Field attachable connectors
- 0,22 mm² - 0,5 mm²

[Inquiry](#)[Show related parts](#)

General Data

Technical Data

Material Data

Downloads

Shielding	Shielded
Wire cross section	0,22 mm ² - 0,5 mm ²
min. working temperature	-40° C
max. working temperature	+85° C
Pollution degree	3/2
IP rating	IP67 in mated condition
Sealing material	Elastomere
Recommended torque	0,6 Nm
Insulation resistance	>=100M Ohm

Suitable Products

