

Image gallery

3D view



Part No: 43-01060

SAL-12-FKH4-P12-9

Product Description

- Sockets
- Female connector axial
- M12x1
- 4- pos.
- 12 mm
- Back panel mounting
- Solder pin
- A-coded
- Unshielded

Inquiry

General Data

Technical Data

Material Data

Standards

Downloads

Shielding	Unshielded
min. working temperature	-30° C
max. working temperature	+80° C
Pollution degree	3/2
IP rating	IP67
Sealing material	FPM
Mating cycles	>=100
Recommended torque	0,6 Nm
Insulation resistance	>=100M Ohm