



Part No: 43-02119

SAL-12S-ISS/SMT

Product Description

- Sockets
- Installation components
- Insulation body
- Male connector axial
- M12x1
- 5- pos.
- 9 mm
- Front panel mounting
- SMT
- A-coded
- Shielded

Inquiry

Show related parts

General Data	Technical Data	Material Data	Standards	Downloads
Shielding	Shielded			
min. working temperature	-25° C			
max. working temperature	+95° C			
Pollution degree	3/2			
IP rating	IP67			
Sealing material	FPM			
Mating cycles	≥100			
Recommended torque	0,6 Nm			
Insulation resistance	≥100M Ohm			

Suitable Products

