






Technical specification :

Rated voltage:	60 V
IEC 61076-2-101	
Current rating:	4 A at 40°C
IEC 61076-2-101	
Insulation resistance:	>=100 MΩ
IEC 60512	
Pollution degree:	3/2
IEC 60664-1	
Degree of protection:	IP 67, in mated condition
IEC 60529	
Temperature range:	-30°C ... +80°C
IEC 60664-1	
Mating cycles:	>=100
IEC 60512-9a	
Materials:	
Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU GF, UL 94
Sealing:	FPM
Coupling nut / screw:	GD-Zn, nickel plated
Moulding body:	TPU, UL 94, grey


Installation specification:

Recommended torque:	0,6 Nm
Contact assignment:	
Conec installation tool:	Torque wrench: 36-000200
	Insert across flats 13: 36-000220



Part no:	Description:	Length L:	Cable:
43-12607	SAL - 12 - DS5 - 2RKW5.2 - 0,3 / 0,3 / K1	0,3m	TPE, UL 20549, black, 4x0,34mm ² Cable: 781-K13500
43-12608	SAL - 12 - DS5 - 2RKW5.2 - 0,6 / 0,6 / K1	0,6m	
43-12609	SAL - 12 - DS5 - 2RKW5.2 - 1,5 / 1,5 / K1	1,5m	
43-12610	SAL - 12 - DS5 - 2RKW5.2 - 3 / 3 / K1	3,0m	
43-xxxxx	SAL - 12 - DS5 - 2RKW5.2 - ... / ... / K1	x	

D see data sheet cable

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	Index: c 17.08.11 VF Ä3767 Coupling nut/ screw modified, spanner flats added, data sheet modified	 dim. in mm	title: Duo-distributor, male connector M12x1 axial - 2x female connector M12x1 angled	
	tolerance of cable: L ≤ 4m: L + 40mm L > 4m: L + 1%			
	general tolerance: 0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm		dwg no: 43K1A791	
	THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH		part no: see table	

