

Image gallery

3D view



Part No: 49-100023

Product Description

- PC104+
- Socket with pin length 12mm
- 120-pos.
- Press-fit

[Inquiry](#)

General Data

Technical Data

Material Data

Standards

Downloads

min. working temperature	-55° C
max. working temperature	+95° C
Quality class	Quality class 3
Mating cycles	50
IP rating	IP 20
Insertion force	180 N
Extraction force	36 N
Contact resistance standard	max. 20 mOhm