

6

5

4



3

2

1

used for:

PC 104



POS. (n)	Part No.
40	49-100080
48	49-100070
64	49-100060
100	49-100050

Directive 2002/95/EC
„RoHS“
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

tolerance		 dim. in mm
2008	date	
drawn	18.11.	E.Mickenbecker
appd.	19.11.	J.Lehmenkühler
norm		
d-old		
a	Origin	
rev.	description	date
		name

CONEC

scale:	2:1
material:	PBT GF Ul 94 V0
title:	
Shroud PC 104 40-100pos.	
dwg no:	AutoCAD 2006
49K1A021	
part no:	SEE TABLE

DIN-A
3
sh: 1/1