



Part No: 6017W2SAM61B50X

Product Description

- IP67 Combination D-SUB
- 17W2 [ø.....ø]
- Socket

[Inquiry](#)

General Data	Technical Data	Material Data	Standards	Downloads
Dielectric with standing voltage signal	1000 V			
Dielectric with standing voltage power	1000 V			
min. working temperature	-25° C			
max. working temperature	+105° C			
Power contact cross section	AWG 16- 20			
Working voltage power	250 V			
Quality class	Quality class 3			
Mating cycles	50			
IP rating	IP67			
Current rating power	10 A			
Extraction force	17 N			
Contact resistance standard	10 mOhm			
Power resistance standard	2,7 mOhm			