

Image gallery

3D view



Part No: 602W2CSXX61B30X

Product Description

- IP67 Combination D-SUB
- 2W2C [o/o]
- Socket

[Inquiry](#)

General Data

Technical Data

Material Data

Standards

Downloads

Dielectric with standing voltage power	1000 V
min. working temperature	-25° C
max. working temperature	+105° C
Power contact cross section	AWG 16- 20
Working voltage power	250 V
Quality class	Quality class 3
Mating cycles	50
IP rating	IP67
Current rating power	10 A
Insertion force	14 N
Extraction force	14 N
Power resistance standard	2,7 mOhm