



Part No: 6STD25SCR99E10X

Product Description

- IP67 D-SUB
- 25-pos.
- Socket
- Solder pin straight

Inquiry

General Data	Technical Data	Material Data	Standards	Downloads
Dielectric with standing voltage signal	1000 V			
Quality class	Quality class 1			
Mating cycles	500			
IP rating	IP67			
Insertion force	83 N			
Extraction force	83 N			
Contact resistance standard	10 mOhm			
min. working temperature	-25° C			
max. working temperature	+105° C			