
Image gallery | 3D view







Part No: 8F8SPA28S58K40X

Product Description

- Filter Combination D-SUB
- 8W8 [oooooooo]
- Plug
- C-Filter
- 100 nF
- Threaded Insert

Inquiry

General Data | Technical Data | Material Data | Standards | Downloads

Dielectric with standing voltage power	707 V DC
Capacitor value power contact	100 nF
Working voltage power	100 V DC
Quality class	Quality class 3
Mating cycles	50
IP rating	IP 20
Current rating power	40 A
Insertion force	56 N
Extraction force	56 N
min. working temperature	-55° C
max. working temperature	+125° C
Filter type	C