

Image gallery

3D view



Part No: CPH47W23FGRASK9X

Product Description

- CompactPCI
- Female Connector
- 24x Signal+23x Power

Inquiry

General Data

Technical Data

Material Data

Standards

Downloads

Dielectric with standing voltage signal	1000 V r.m.s.
Dielectric with standing voltage power pos.1-20	1500 V r.m.s.
Dielectric with standing voltage power pos.45-47	3000 V r.m.s.
IP rating	IP 20
Current rating power pos. 1-20	28 A
Current rating power pos. 45-47	40 A
Working voltage power 1-20	500 V r.m.s.
Working voltage power 45-47	1000 V r.m.s.
min. working temperature	-55° C
max. working temperature	+125° C
Contact resistance standard	0,004 Ohm
Power resistance standard	0,0007 Ohm
Quality class	Quality class 3
Mating cycles	50
Insulation resistance	5 GOhm