

Image gallery

3D view



Part No: DLS1PS5AN21X

Product Description

- D-SUB Dual Port
- Dual port 9-pos. / 9-pos.
- Dual port plug upper / Socket bottom
- Solder Pin angled Dual Port .625" stamped Contacts
- Metal bracket
- Quality class 3
- UNC 4-40

Inquiry

General Data

Technical Data

Material Data

Standards

Downloads

Dielectric with standing voltage signal	1000 V
Quality class	Quality class 3
Mating cycles	50
IP rating	IP 20
Insertion force	<30 N
Extraction force	<30 N
min. working temperature	-55° C
max. working temperature	+125° C