



Part No: DLS5XS4AA39X

Product Description

- D-SUB Standard
- 50-pos.
- Socket
- Solder Pin stamped Contacts
- Threaded rear spacer
- Quality class 3
- UNC 4-40

[Inquiry](#)

General Data

Technical Data

Material Data

Standards

Downloads

Dielectric with standing voltage signal	1000 V
Quality class	Quality class 3
Mating cycles	50
IP rating	IP 20
Insertion force	<167 N
Extraction force	<167 N
min. working temperature	-55° C
max. working temperature	+125° C