



+ RELAYS, CONTACTORS & SWITCHES

MID-RANGE



✓ Active

TE CONNECTIVITY (TE)

FCB-205-0123M=M83536/1-023M

CII | FCB 5-10 Amp Relay

FCB-205-0123M

TE Internal Number: 3-1617758-2

Mil-Spec: M83536/1-023M

Not EU RoHS Compliant

Not EU ELV Compliant

Contact Arrangement 2 Form C, DPDT, 2 C/O

Coil Suppression Diode Without

Auxiliary Contacts Without

Terminal Plating Tin-Lead

Contact Current Rating (A) 5

↓ PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

FCB-205-0123M=M83536/1-023M

PDF

English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Terminal Configuration Solder Hook
Relay Type Military/Aerospace Mid-Range
Enclosure Type Hermetically Sealed
Product Type Relay

Electrical Characteristics

Coil Suppression Diode Without
Coil Voltage Rating (VDC) 28
Coil Resistance (Ω) 500
Back EMF Suppression Without
Coil Magnetic System Polarized, Monostable
Actuating System DC
Shock 200G's, 6ms
Vibration 30G's, 70 – 3000Hz

Contact Features

Contact Arrangement 2 Form C, DPDT, 2 C/O
Auxiliary Contacts Without
Terminal Plating Tin-Lead
Contact Current Rating (A) 5
Contact Base Material Silver Cadmium Oxide

Mechanical Attachment

Mounting Type Raised Vertical Flange Mount

Usage Conditions

Operating Temperature Range ($^{\circ}\text{C}$) -70 – 125

Statement of Compliance

Statement of Compliance

PDF
