


## FCA - 325 - CX2 Product Details



**FCA - 325 - CX2**

[Active](#)

### Military/Aerospace Mid - Range Relays

[Not EU RoHS or ELV Compliant](#)

#### Product Highlights:

- ? FCA 10-25 Amp Relay Series
- ? DC Actuating System
- ? Coil Voltage = 12 VDC
- ? Contact Arrangement = 3 Form C, 3PDT, 3 C/O
- ? Current Rating = 25 Amps.

[View all Features](#) | [Find Similar Products](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [MSD RELAY](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? None Available

#### Instruction Sheets:

- ? None Available

#### CAD Files:

- ? None Available

#### Additional Information:

- ? [Product Line Information](#)

#### Additional Product Images:

- ? [Dimensional Drawing](#)
- ? [Wiring Diagram](#)
- ? [Terminal Type](#)

#### Related Products:

- ? [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? [Terminal Type](#) = Solder Hook

#### Electrical Characteristics:

- ? [Actuating System](#) = DC
- ? [Coil Voltage \(VDC\)](#) = 12
- ? [Current Rating \(Amps.\)](#) = 25

#### Termination Related Features:

- ? [Terminal Plating](#) = Tin -Lead
- ? Auxiliary Contacts = Without

#### Body Related Features:

- ? Series = FCA 10 -25 Amp Relay
- ? [Mount Type](#) = Side Mount

#### Configuration Related Features:

- ? [Contact Arrangement](#) = 3 Form C, 3PDT, 3 C/O
- ? [Coil Suppression Diode](#) = Without
- ? Coil Magnetic System = Polarized, Monostable

#### Industry Standards:

- ? Government/Industry Qualification = No
- ? [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- ? [Lead Free Solder Processes](#) = Not suitable for lead free processing

#### Other:

- ? Brand = CII