



Expulsion fuse-link, medium voltage, 75 A, AC 15 kV, 8 kA, 533 mm, ANSI, fixed NEMA button head link, K fast

Part no. 15KV 75A EXPULSION LINK
Catalog No. 15KB75

Similar to illustration

Delivery program

Product range			Fuse
Basic function			Expulsion fuse-link
Field of application			medium voltage
Rated current	I	A	75
Rated voltage			AC 15 kV
Size			533 mm
Description			fixed NEMA button head link
Breaking Capacity		kA	8
usable for size/applications			protection of transformer primary side, feeder, capacitor bank
Release characteristic	class		K fast
Standard/Approval			ANSI
Standards/Regulations			ANSI C37-42

Technical data ETIM 8.0

Circuit breakers and fuses (EG000020) / Expulsion fuse-link, medium voltage (EC003611)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Safety fuse systems (unspecified) (ecl@ss10.0.1-27-14-21-90 [BAB265011])			
Rated current		A	75
Rated voltage		kV	15
Voltage type			AC
Rated frequency		Hz	50 - 60
Release characteristic			K
Type of termination			Fixed buttonhead
Standard			ANSI