

Specifications



Eaton CGL-30

Eaton Bussmann series Tron CGL HRC form II Class C fuse, 600 Vac, 250 Vdc, 30A, 200 kAIC at 600 Vac, 40 kAIC 250 Vdc, Non Indicating, Current-limiting, HRC Form II, Blade end X blade end, Class C

General specifications

PRODUCT NAME	Eaton Bussmann series CGL fuse
CATALOG NUMBER	CGL-30
UPC	051712100328
PRODUCT LENGTH/DEPTH	0.81 in
PRODUCT HEIGHT	3.31 in
PRODUCT WIDTH	0.94 in
PRODUCT WEIGHT	0.115 lb
WARRANTY	Not Applicable
COMPLIANCES	Not Applicable
GLOBAL CATALOG	CGL-30



Powering Business Worldwide

Product specifications

AMPERAGE RATING	30 A
CLASS	Class C
INTERRUPT RATING	200 kAIC at 600 Vac 40 kAIC 250 Vdc
FUSE INDICATOR	Non-indicating
CONNECTION	Blade end x blade end
PACKAGING TYPE	Standard
VOLTAGE RATING	600 Vac, 250 Vdc
TYPE	Current-limiting, HRC Form II

Resources

	Bussmann series complete full line catalog no. 1007
CATALOGS	Bussmann series full line catalog 1007, section 05-IEC and British Standard fuses
	BS88 fuse link portfolio
MULTIMEDIA	Bussmann series Fuseology
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CGL-30
	CGL-30~LIMITRON FAST ACTING FUSE
TECHNICAL DATA SHEETS	Bussmann series CGL HRCII-C current-limiting fuses data sheet no. 4125
TECHNICAL SERVICE BULLETINS	Datasheet - FNQ-30

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

