

Eaton CHM1DNIU

Eaton Bussmann series CHM modular fuse holder, 600V (UL), 690V (IEC), 30A (UL), 32A (IEC), 200 kAIC, Modular fuse holder, Single-pole - CHM1DNIU

General specifications

PRODUCT NAME	Eaton Bussmann series CHM modular fuse holder
CATALOG NUMBER	CHM1DNIU
UPC	051712362764
EAN	51712362764
PRODUCT LENGTH/DEPTH	0.001 mm
PRODUCT HEIGHT	0.001 mm
PRODUCT WIDTH	0.001 mm
PRODUCT WEIGHT	113 g
WARRANTY	Not Applicable
COMPLIANCES	Contact factory RoHS Compliant
CERTIFICATIONS	Contact Manufacturer

Electrical rating

AMPERAGE RATING	30A (UL), 32A (IEC)
INTERRUPT RATING	200 kAIC
VOLTAGE RATING	600 V (UL), 690 V (IEC)

General information

USED WITH	For use with 10 mm X 38 mm fuse
------------------	---------------------------------

Physical details

NUMBER OF POLES	Single-pole
OPERATING TEMPERATURE - MAX	90 °C
OPERATING TEMPERATURE - MIN	-20 °C
WIRE SIZE	#18-4 AWG

Resources

DECLARATIONS OF CONFORMITY	UKCA Modular fuse-holders CE Modular fuse-holders
DRAWINGS	Eaton Power Distribution CHM Modular Fuse Holder CAD Drawing CHM1DNIU
MULTIMEDIA	Bussmann series Fuseology
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CHM1DNIU
TECHNICAL DATA SHEETS	720147 10 x 38 mm Modular fuse holder

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

