

Specifications

Photo is representative

Eaton HLS-02

Eaton Bussmann series HLS fuse holder, No flanges, 125 Vac, 60 Vdc, 15 A, Two-pole, Tin-plated bifurcated copper terminal

General specifications

PRODUCT NAME	Eaton Bussmann series HLS fuse holder
CATALOG NUMBER	HLS-02
UPC	051712169905
PRODUCT LENGTH/DEPTH	0.001 in
PRODUCT HEIGHT	0.001 in
PRODUCT WIDTH	0.001 in
PRODUCT WEIGHT	5.5 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant

Electrical rating

AMPERAGE RATING	15 A
VOLTAGE RATING	125 Vac, 60 Vdc

General information

SPECIAL FEATURES	No flanges
USED WITH	Used with GMT Type Indicating Series

Physical details

MATERIAL	Tin-plated bifurcated copper terminal
NUMBER OF POLES	Two-pole

Resources

CATALOGS	Bussmann series complete full line catalog no. 1007 HLS-02~BUSS MULTIPOLE FUSEHLDR
MULTIMEDIA	Bussmann series Fuseology
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - HLS-02

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

