

# Specifications

Photo is representative

## Eaton JJS-150

Eaton Bussmann series JJS fuse, Current-limiting very fast acting fuse, Small footprint, VFD line protection, 150 A, Class T, Non-indicating, Bolted blade end x bolted blade end, 200 kAIC at 600 V, Standard, 1, 600 V

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series JJS fuse
<b>CATALOG NUMBER</b>	JJS-150
<b>UPC</b>	051712628167
<b>PRODUCT LENGTH/DEPTH</b>	3.25 in
<b>PRODUCT HEIGHT</b>	0.88 in
<b>PRODUCT WIDTH</b>	0.88 in
<b>PRODUCT WEIGHT</b>	0.2 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	CE Marked <a href="#">RoHS Compliant</a>



Powering Business Worldwide

## Electrical rating

<b>AMPERAGE RATING</b>	150 A
<b>INTERRUPT RATING</b>	200 kAIC at 600 Vac
<b>VOLTAGE RATING</b>	600 V

## General information

<b>CLASS</b>	Class T
<b>CONNECTION</b>	Bolted blade end x bolted blade end
<b>FUSE INDICATOR</b>	Non-indicating
<b>QUANTITY</b>	1
<b>SPECIAL FEATURES</b>	Small footprint

## Physical details

<b>PACKAGING TYPE</b>	Standard
-----------------------	----------

## Resources

<b>CATALOGS</b>	<a href="#">Bussmann Full Line Catalog</a> <a href="#">Low Voltage Branch Circuit Fuse Chapter</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">Eaton Bussmann EU Declaration of conformity-93-68-EEC2003</a>
<b>COMPLIANCE INFORMATION</b>	<a href="#">RoHS Search Tool</a>
<b>MULTIMEDIA</b>	<a href="#">Bussmann series Fuseology</a>
<b>TECHNICAL DATA SHEETS</b>	<a href="#">JJS-100~TRON FAST ACTING FUSE CLASS T</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.