

Specifications

Eaton KTK-R-3

Eaton Bussmann Series Class CC fuse, KTK-R, fast-acting, dual-element current limiting fuse, 3 A, rejection style fuse, interrupting rating of 200kA at 600Vac

General specifications

PRODUCT NAME	Eaton Bussmann series KTK-R fuse
CATALOG NUMBER	KTK-R-3
UPC	051712420624
EAN	5027590445634
PRODUCT LENGTH/DEPTH	0.001 in
PRODUCT HEIGHT	0.001 in
PRODUCT WIDTH	0.001 in
PRODUCT WEIGHT	0.15 lb
WARRANTY	Not Applicable
COMPLIANCES	RoHS Compliant CE Marked
CERTIFICATIONS	UL Listed CSA Certified



Powering Business Worldwide

Product specifications

AMPERAGE RATING	3 A
NUMBER OF ELEMENTS	Dual
CLASS	Class CC
INTERRUPT RATING	200 kAIC
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end Ferrule
RESPONSE TIME	See time current curve
MATERIAL	Melamine tube
PACKAGING TYPE	Standard
QUANTITY	10
VOLTAGE RATING	600 V
TYPE	Current-limiting fast-acting fuse
SPECIAL FEATURES	Rejection style
APPLICATION	Industrial controls panels and machinery, street lighting, general lighting, capacitors and distribution

Resources

[Bussmann Full Line
Catalog](#)

[Low Voltage Branch Circuit
Fuse Chapter](#)

CATALOGS

[Bussmann series full line
catalog 1007, section 01-
low voltage branch circuit
fuses](#)

[Bussmann series complete
full line catalog no. 1007](#)

CERTIFICATION REPORTS

[Eaton Bussmann EU
Declaration of conformity
93-68-EEC2000](#)

MULTIMEDIA

[Bussmann series
Fuseology](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet -
KTK-R-3](#)

[KTK-R Spec Sheet](#)

TECHNICAL DATA SHEETS

[KTK-R-3~CLASS CC FAST
ACTING FUSE CLASS CC](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

