

Specifications

Photo is representative

Eaton KTN-R-5

Eaton Bussmann Series Class RK1 fuse, KTN-R, fast-acting, current limiting fuse, 5 A, rejection style fuse, interrupting rating of 200 kA at 250 Vac

General specifications

PRODUCT NAME	Eaton Bussmann series KTN-R fuse
CATALOG NUMBER	KTN-R-5
UPC	051712407298
EAN	5027590446211
PRODUCT LENGTH/DEPTH	2 in
PRODUCT HEIGHT	0.56 in
PRODUCT WIDTH	0.56 in
PRODUCT WEIGHT	0.045 lb
WARRANTY	Not Applicable
COMPLIANCES	Not Applicable



Powering Business Worldwide

Electrical rating

AMPERAGE RATING	5 A
VOLTAGE RATING	250 V

General information

CLASS	Class RK1
CONNECTION	Ferrule end x ferrule end
FUSE INDICATOR	Non-indicating
SPECIAL FEATURES	70/30 brass end cap

Physical details

MATERIAL	Melamine glass tube
NUMBER OF ELEMENTS	1
PACKAGING TYPE	Standard

Resources

CATALOGS	Bussmann Full Line Catalog Low Voltage Branch Circuit Fuse Chapter
COMPLIANCE INFORMATION	RoHS Search Tool
MULTIMEDIA	Bussmann series Fuseology
TECHNICAL SERVICE BULLETINS	Bussmann series KTN-R 250 V Class R fuse data sheet no. 1043

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.