

Specifications

Photo is representative

Eaton KU12

Eaton Bussmann KU series panel mount terminal block connector, 600 V, 60 A, Double row, Standard, 12-pole, 10-32 TPI Screw, Black, Nickel-plated brass terminal

General specifications

PRODUCT NAME	Eaton Bussmann KU series panel mount terminal block connector
CATALOG NUMBER	KU12
UPC	051712588782
PRODUCT LENGTH/DEPTH	8.75 in
PRODUCT HEIGHT	1.25 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	0.4 lb
WARRANTY	Not Applicable
COMPLIANCES	Not Applicable RoHS Compliant
CERTIFICATIONS	Contact Manufacturer

Electrical ratings

AMPERAGE RATING	60A
VOLTAGE RATING	600 V

Physical details

NUMBER OF POLES	Twelve-pole
TYPE	Double row, standard

Resources

CATALOGS	KU12~TERM BLOCK BLACK NOR Bussmann series complete full line catalog no. 1007
MULTIMEDIA	Bussmann series Fuseology

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

