

Specifications

Photo is representative

Eaton MIC-20

Eaton Bussmann series MIC fuse, Fast acting, Midget fuse, Control circuits, PLC circuits, Electronic circuits, 20 A, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 32 Vac, Nickel-plated bronze endcap, Fiber tube, Standard, 32 V

General specifications

| | |
|-----------------------------|--------------------------------|
| PRODUCT NAME | Eaton Bussmann series MIC fuse |
| CATALOG NUMBER | MIC-20 |
| UPC | 051712726481 |
| EAN | 5027590450188 |
| PRODUCT LENGTH/DEPTH | 0.47 in |
| PRODUCT HEIGHT | 1.813 in |
| PRODUCT WIDTH | 0.47 in |
| PRODUCT WEIGHT | 0.15 lb |
| WARRANTY | Not Applicable |
| COMPLIANCES | Not Applicable |



Powering Business Worldwide

Electrical rating

AMPERAGE RATING 20 A

INTERRUPT RATING 10 kAIC at 32 Vac

VOLTAGE RATING 32 V

General information

CONNECTION Ferrule end x ferrule end

FUSE INDICATOR Non-indicating

Physical details

MATERIAL Nickel-plated bronze
endcap
Fiber tube

PACKAGING TYPE Standard

Resources

[MIC-20~BUSS MIDGET
FUSE INDICATING](#)

CATALOGS

[Bussmann series complete
full line catalog no. 1007](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet -
MIC-20](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

