

Specifications

Photo is representative

Eaton TB200HB-12

Eaton Bussmann TB200 series panel mount terminal block connector, Breakdown voltage 4800V, 600V, 30A, Double row, high barrier, Twelve-pole, #6-32 TPI Screw, Black, Tin-plated brass terminal, Zinc-plated Steel philslot screw

General specifications

PRODUCT NAME	Eaton Bussmann TB200 series panel mount terminal block connector
CATALOG NUMBER	TB200HB-12
UPC	051712602327
PRODUCT LENGTH/DEPTH	6 in
PRODUCT HEIGHT	0.75 in
PRODUCT WIDTH	1.37 in
PRODUCT WEIGHT	0.7 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	Contact Manufacturer



Powering Business Worldwide

Electrical ratings

AMPERAGE RATING	30A
VOLTAGE RATING	600 V

Physical details

NUMBER OF POLES	Twelve-pole
TYPE	Double row, high barrier

Resources

CATALOGS [Bussmann series complete full line catalog no. 1007](#)

[TB200HB-12~BARRIER BLOCK](#)

CERTIFICATION REPORTS [Eaton Bussmann EU Declaration of conformity 93-68-EEC2617](#)

MULTIMEDIA [Bussmann series Fuseology](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

