

Specifications

Eaton TB300-12



Eaton Bussmann TB300 series panel mount terminal block connector, Breakdown voltage 7500V, 600V, 30A, Double row, barrier, Twelve-pole, #8-32 TPI Screw, Screw, Black, Tin-plated brass terminal, Zinc-plated Steel philslot screw

Photo is representative



General specifications

PRODUCT NAME	Eaton Bussmann series TB300 panel mount terminal block
CATALOG NUMBER	TB300-12
UPC	051712810630
PRODUCT LENGTH/DEPTH	7.75 in
PRODUCT HEIGHT	0.81 in
PRODUCT WIDTH	1.33 in
PRODUCT WEIGHT	0.16 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	Contact Manufacturer



Powering Business Worldwide

Electrical ratings

AMPERAGE RATING	30A
VOLTAGE RATING	600 V

Physical details

NUMBER OF POLES	Twelve-pole
TYPE	Double row, barrier

Resources

CATALOGS	Bussmann series full line catalog 1007, section 10 - connector products
-----------------	---

CERTIFICATION REPORTS	Eaton Bussmann EU Declaration of conformity 93-68-EEC2617
------------------------------	---

MULTIMEDIA	Bussmann series Fuseology
-------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

