

# Specifications

## Eaton TB345-04



Eaton Bussmann TB345 series panel mount terminal block connector, Breakdown voltage 7500V, 600V, 45A, Double row, barrier, Four-pole, #10-32 TPI Screw, Screw, Black, Tin-plated brass terminal, Zinc-plated Steel philslot screw



### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series TB345 panel mount terminal block
<b>CATALOG NUMBER</b>	TB345-04
<b>UPC</b>	051712812535
<b>PRODUCT LENGTH/DEPTH</b>	3.25 in
<b>PRODUCT HEIGHT</b>	0.81 in
<b>PRODUCT WIDTH</b>	1.33 in
<b>PRODUCT WEIGHT</b>	0.116 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	RoHS Compliant CE Marked
<b>CERTIFICATIONS</b>	Contact Manufacturer



Powering Business Worldwide

## Electrical ratings

**AMPERAGE RATING** 45 A

**VOLTAGE RATING** 600 V

## Physical details

**NUMBER OF POLES** Four-pole

**TYPE** Double row, barrier

## Resources

[TB345-04-BARRIER BLOCK](#)

### CATALOGS

[Bussmann series complete full line catalog no. 1007](#)

### CERTIFICATION REPORTS

[Eaton Bussmann EU Declaration of conformity 93-68-EEC2617](#)

### MULTIMEDIA

[Bussmann series Fuseology](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

