

75KEMS10ABSD

✓ ACTIVE

Corcom | Corcom KEM


TE Internal #: 3-1609967-4

75 A 3-Phase Filter, Terminal Block Input, Terminal Block Output, DELTA (3 wire + ground), 440 VAC, Chassis Mount, Corcom KEM

[View on TE.com >](#)



EMI & EMC Solutions > EMC Filters > Power Line Filters > 3-Phase Filters > 3 Phase General Purpose EMI Filters, KEM



Current Rating: 75 A

Input Termination Type: Terminal Block

Output Termination Type: Terminal Block

Wiring Configuration: DELTA (3 wire + ground)

Operating Voltage: 440 VAC

[All 3 Phase General Purpose EMI Filters, KEM \(89\)](#)

Features

Product Type Features

Filtering Requirements	Filtered
Input Termination Type	Terminal Block
Output Termination Type	Terminal Block

Configuration Features

Wiring Configuration	DELTA (3 wire + ground)
----------------------	-------------------------

Electrical Characteristics

Leakage Current (Max) (230VAC, 50Hz)	10
Current Rating	75 A
Operating Voltage	440 VAC

Mechanical Attachment

Product Mount Type	Chassis Mount
--------------------	---------------

Usage Conditions

Operating Temperature Range	-25 – 85 °C
-----------------------------	-------------



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	未针对中国 RoHS 符合性进行审核 Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) SVHC > Threshold: Pb (3% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-F83-KEM
3 Phase General Purpose EMI Filters, KEM

Also in the Series | Corcom KEM



3-Phase Filters(89)

Customers Also Bought



TE Part #535090-4
096 EURO TYPE C RECEPT ST ASSY




TE Part #2-644488-6
06P MTA100 SHRD HDR F/L R/A SN




TE Part #6-1393252-1
W67-X2Q12-30=M6/M7/M9/W6/W7




TE Part #7-1625890-0
2W SM M/OX 5% 82K



TE Part #5-1879666-4
H8 475K 0.1% 15PPM



TE Part #7-2176316-2
MELF SMA_A 68K 1% 50PPM 0207 1W



TE Part #8-2176316-9
MELF SMA-A 120K 1% 50PPM 0207 1W



TE Part #5-1437595-2
TRD11F10WL=SUB MINI ROCKER BLA



TE Part #1-1393766-9
R10-E1X4-24V=R10



TE Part #1-1393767-5
R10-E2X2-V700=R10

Documents

Product Drawings

KEM 75A 1S HIGH PER SP BS DELTA 440VAC

English

CAD Files

Customer View Model

ENG_CVM_CVM_3-1609967-4_B.3d_igs.zip

English

Customer View Model

75KEMS10ABSD

75 A 3-Phase Filter, Terminal Block Input, Terminal Block Output, DELTA (3 wire + ground), 440 VAC, Chassis Mount, Corcom KEM



[ENG_CVM_CVM_3-1609967-4_B.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-1609967-4_B.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

KEM-BS SERIES

English