

[Skip to content](#)

Search By: Part Number Text [Tips](#)



Sunday, September 10, 2006

[Sign In](#)

[Home](#) > [Products](#) > [By Type](#) > [PolySwitch Resettable Devices](#) > [Product Feature Selector](#) > Product Details

Product Details for RXEF040-2



RXEF040-2

Tyco Part Number: D27406-000



[Active](#)

PolySwitch Resettable Devices



[RoHS Compliant](#)

Product Highlights:

- Radial Application
- Family Name = RXEF
- Through Hole Construction
- Radial Construction
- IH (Room Temperature) = .4 Amps.

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [RXEF040](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- UL Recognized = File No. E74889

Electrical Characteristics:

- [IH \(Room Temperature\) \(Amps.\)](#) = 0.4
- [IT \(Room Temperature\) \(Amps.\)](#) = 0.80
- [Vmax Operating \(V\)](#) = 72
- [Rmin \(\)](#) = 0.55
- [Rmax \(\)](#) = 0.860
- [R1 Max \[Post Trip\] \(\)](#) = 1.29
- [UL Rated Current \(Amps.\)](#) = 40
- Tripped Power Dissipation (Typical) (W) = 0.56

Termination Related Features:

- Construction = Radial, Through Hole

Body Related Features:

- Lead Type = Standard Kinked Lead
- CSA File No. = 78165C

Contact Related Features:

- Family Name = RXEF

Configuration Related Features:

- Coating = Coated

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant
- TUV Certificate No. = R72041428

Conditions for Usage:

- [Operating Temperature \(Max.\) \(°C\)](#) = 85

Operation/Application:

- Application = Radial

Packaging Related Features:

- Packaging Method = Tape & Reel

Other:

- Brand = Raychem

Languages: English | [Deutsch](#) | [Español](#) | [Português \(do Brasil\)](#) | _____ | [Italiano](#) | [正體中文 \(繁體\)](#) | [中文 \(简体\)](#) | [日本語](#)

Country Sites: [China](#) | [Japan](#)

© 2006 Tyco Electronics All Rights Reserved

[Home](#) | [Customer Support](#) | [Supplier](#) | [Site Map](#) | [Privacy Policy](#) | [Browser Support](#)